



Filter mat, Extract: W: 177 mm, H: 177 mm, IP54, Quality class G3

Model		
product brand name		SIVACON
product designation		filter mat
design of the product		Class G3
fan design withdrawable fan		No
design of the product EMC version		No
General technical data		
cutout width		177 mm
cutout height		177 mm
Protection class		
protection class IP		IP54
Product details		
product component fan		No
Mechanical Design		
height		171 mm
width		171 mm
installation location		Control cabinet side panels, door, vertical
fastening method		snap-on mounting
fastening method		
• 19-inch installation		No
• wall mounting		Yes
net weight		0.1 kg
material		plastic
ambient temperature during operation		
• minimum		-10 °C
• maximum		55 °C
Approvals Certificates		
General Product Ap- proval	other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6000-0AM30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6000-0AM30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6000-0AM30

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

