

Hager Product Data Sheet

XVR107STP

witty one EV Charging Station 1x7 kW, 1 Phase + N, Type 2S Socket, TIC, FR Protections

Translated from the French technical data sheet dated 07/02/2026.

Category	Specification
Power	Maximum power per charging point: 7 kW Connected power: 0.1 - 7 kW
Frequency	50 - 60 Hz
Power supply	1 phase
Rated current	32 A
Charging points	1
Load management	Yes
Equipment	Domestic sockets: 0 Protective circuit breaker: Yes Emergency trip on power failure: Yes
Connection	Type 2S
Dimensions	370 x 250 mm Height: 370 mm Width: 250 mm Depth: 150 mm
Installation	Wall mounted
Protection	IP55 IK10
Operating temperature	-25 to +50 °C
Voltage	230 V
Material	Plastic
RoHS compliant	Yes

Product visual available in the original French datasheet: ■image placeholder■