

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Full Metal Construction
- Available in different sizes

RS PRO ESD Worktable 1200x700, 1200x800, 1200x900 H-type

RS Stock No.: 0687726

0687727

0687728



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO ESD Workstation

The H System is a robust and ergonomic workstation designed for demanding work environments such as warehouses, workshops, and production lines. Made from high-quality structural steel, it offers a load capacity of up to 300 kg (500 kg in reinforced version). With manual height adjustment from 750 to 1100 mm and full ESD protection, it ensures user comfort, safety, and flexibility. Its modular design allows for easy expansion and customization to meet specific workspace needs.

General Specifications

WIDTH (mm)	1200
DEPTH (mm)	900
WEIGHT (kg)	38
MAX LOAD (kg)	300
TYPE OF HEIGHT ADJUSTMENT (mm)	MANUAL 50 mm STEP
ESD	YES
COLOUR	RAL 7035 (LIGHT GREY) RAL 9005 (BLACK)
MATERIAL OF TABLE FRAME	CONSTRUCTION STEEL
TABLETOP	DOUBLE SIDED ANTISTATIC, DISSIPATIVE, WITH GRAPHITE ADDITIVE, COVERED WITH A MELAMINE LAYER, THICKNESS 25 mm
TYPE OF GLIDES	SELF-LEVELLING
RESISTANCE GROUNDING (0hm)	$10^4 - 10^8$

Available in the following versions:

Stock No.	Brand	Product Name	Width	Depth
0687726	RS PRO	ESD worktable 1200x700, H-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1200	700
0687727	RS PRO	ESD worktable 1200x800, H-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1200	800
0687728	RS PRO	ESD worktable 1200x900, H-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1200	900

Similar Products

Stock No.	Brand	Product Name	Width	Depth
0687760	RS PRO	ESD worktable 1500x700, H-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1500	700
0687654	RS PRO	ESD worktable 1800x700, H-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1800	700
0687678	RS PRO	ESD worktable 2000x700, H-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	2000	700
0687729	RS PRO	ESD worktable 1200x700, L-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1200	700
0687763	RS PRO	ESD worktable 1500x700, L-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1500	700

0687658	RS PRO	ESD worktable 1800x700, L-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	1800	700
0687682	RS PRO	ESD worktable 2000x700, L-type, manual height adjustment, table top light grey surface (25mm), with a dark grey plastic edging (1mm), steel powder coated with antistatic paint	2000	700

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories