




Datasheet

Stock No: 297-5899

RS Pro Line Mounting Hydraulic Flow Control Valve, NPT 3/8, 700 bar





Product Details

Isolator Needle Valves

These high pressure isolator needle valves, available in BSP and NPT thread forms, are designed to shut off and control the flow in both directions.

Flow Control Valves

Single acting and double acting in-line flow control valves. Single acting valves allow flow control in one direction and free flow in the opposite direction. Double acting valves allow flow control in both directions.



ENGLISH

Specifications:

| Manufacturer Series | F |
|-------------------------------|--------------|
| Connection Port Thread | G 1/2 |
| Maximum Flow Rate | 40L/min |
| Body Material | Carbon Steel |
| Seal Material | PTFE |
| Maximum Operating Pressure | 700 bar |
| Thread Size | 1/2 in |
| Thread Standard | G |
| Maximum Operating Temperature | +240°C |
| Minimum Operating Temperature | -20°C |