

Features

- **Elastic Slip-On Design** – Quick and easy application with a full-diameter elastic rim for secure fit.
- **Ventilated Mesh Material** – Allows airflow while keeping out debris, pests, and contaminants.
- **Integrated Warning Signage** – Bold, printed caution message enhances safety awareness on-site.
- **High-Traffic Durability** – Made from strong, perforated polyester mesh for rugged use in industrial settings.
- **Reusable & Easy to Clean** – Washable material ensures long-term usability across multiple operations.
- **Compact & Lightweight** – Folds easily for convenient storage and transportation.

Product Description

RS PRO Elastic Non-Lockable Ventilated Confined Space Cover - Small (22" ø)

RS Stock No.: 0694372



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *Elastic Non-lockable Ventilated Confined Space Covers offer a fast, easy slip-on and slip-off application, making it a perfect solution for preventing unauthorized entry into confined spaces during maintenance, shutdowns, and daily operations.*
- *Constructed from durable, perforated polyester mesh, suitable for high-traffic industrial environments.*
- *Features a full-circumference elastic band for slip-on/slip-off application over confined space flanges.*
- *Built-in warning signage provides a clear visual hazard alert to passers-by and workers.*
- *Mesh material allows natural ventilation while blocking debris, trash, and pests from entering.*
- *Reusable, lightweight, and easily foldable—perfect for quick deployment and compact storage.*
- *Reusable covers are easily cleaned and stored.*
- *Compact and lightweight for easy transport and storage.*
- *Covers manufactured in bright red colour for high visibility.*

General Specifications

Type	Non-Lockable Confined Space Lockout Cover
Material	Nylon Mesh
Colour	Red & Black
Package	BOPP + Bag

Mechanical Specifications

Diameter	559mm (22")
Weight	490 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 80°C
------------------------------	---------------