



Product data sheet

Power tools for trade & industry

Reciprocating Saw

PRO GSA 12-30



An ergonomic saw, much faster now for your demolition work

The most important data

Rated input power	1,250 W
Stroke length	30 mm
Weight	3.7 kg

Part Number 0 601 6C7 070

Technical data

Technical data

Rated input power	1,250 W
Weight	3.7 kg
Stroke length	30 mm
Packaging dimensions (width x length x height)	129 x 565 x 298 mm
Voltage, electrical	230 V
Cut thickness, wood	220 mm
Cut thickness, steel	20 mm

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Optimized tool vibration that enables quick and smooth cutting into materials especially in metal pipes
- Improved ergonomic rear and front gripping area design offers users a comfortable cutting experience in any position
- Powerful motor and long 30mm stroke for improved cutting speed



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

