

Han Q4/2 Bu Daisy Chain Y-Distributor



Image is for illustration purposes only. Please refer to product description.

Part number	61 88 201 0509 01
Specification	Han Q4/2 Bu Daisy Chain Y-Distributor
HARTING eCatalogue	https://harting.com/6188201050901

Identification

Identification	4/2
Element	Y-distributor

Version

Termination method	Cage-clamp termination
Number of contacts	3
PE contact	Yes
Field of application	Power cables

Technical characteristics

Conductor cross-section	1.5 ... 4 mm ² Spring clamp termination
Conductor cross-section [AWG]	AWG 20 ... AWG 12 Spring clamp termination
Rated current	32 A 20 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65
Test voltage U _{r.m.s.}	6 kV

Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 9005 (jet black)
Material (cable glands)	Thermoplastic
Colour (cable gland)	Black
Material (seal)	Elastomer
Colour (seal)	White
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	230 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140161498
eCl@ss	27142409 Small distribution board
ETIM	EC000214
UNSPSC 24.0	39121303