

Product data sheet

Specifications



Spacial SM compact enclosure without mounting plate - 1800x600x400 mm

NSYSM18640

Main

| | |
|-----------------------------|-----------------------------------------------------------------------------------------------------------|
| Range | Spacial |
| Product name | Spacial SM |
| Product or component type | Compact enclosure |
| Application | Multi-purpose |
| Installation accessory type | Floor-standing |
| Device composition | 1 body 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket 1 door |
| Removable parts | Door by screws hinge Mounting plate bracket by screws |
| Enclosure nominal height | 1800 mm |
| Enclosure nominal width | 600 mm |
| Enclosure nominal depth | 400 mm |

Complementary

| | |
|-----------------------------|--------------------------------------------------------------------------------------------------|
| Number of doors | Front: 1 door(s) |
| Door opening side | Reversible (120 °) |
| Door type | Plain |
| Lock type | 4 points lock, handle with 5 mm double bar insert |
| Body type | Single piece body with welded rear panel Front part forming a rigid frame with welded corners |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Standard |
| Cable entry | 1 entry |
| Material | Body: sheet steel Door: sheet steel Hinge: zamak |
| Surface finish | Epoxy-polyester powder |
| Colour | Enclosure: grey (RAL 7035) Handle: black (RAL 9005) |
| Accessibility for operation | Front |
| Net weight | 79.5 kg |

Environment

| | |
|-------------------------|------------------------------|
| Standards | IEC 62208 |
| Product certifications | UL BV DNV |
| IK degree of protection | IK10 conforming to IEC 62262 |
| IP degree of protection | IP55 conforming to IEC 60529 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 79.5 kg |
| Package 1 Height | 193 cm |
| Package 1 width | 64.5 cm |
| Package 1 Length | 49 cm |

Offer Sustainability

| | |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|