

Han 1A-3+PE-c-m shielded



Image is for illustration purposes only. Please refer to product description.

Part number	09 10 003 3006
Specification	Han 1A-3+PE-c-m shielded
HARTING eCatalogue	https://harting.com/09100033006

Identification

Category	Inserts
Series	Han [®] 1A

Version

Termination method	Crimp termination
Gender	Male
Size	1 A
Shielding	With cable tie
Number of contacts	3
further contacts	+ shielding
PE contact	Yes
Locking type	Single locking lever
Details	Please order crimp contacts separately. Please order locking lever separately. Order separately the hoods/housings for an IP65 performance.

A Han[®] 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector according to IEC 61984. In this case protection against electric shock must be provided by the installation methods of the user.

Details

The Han[®] 1A insert has no conductive connection between PE-contact and shielding element. Protection against electric shock must be provided by connecting the cable shielding to a protective earth (PE).

Contact inserts must not be coupled or decoupled under electrical load.

Contact inserts must not be powered-up in the un-mated condition.

Pack contents	Shielding element is included within the delivery
---------------	---



Pushing Performance
Since 1945

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated current acc. to UL	15 A AWG 14
Rated voltage acc. to UL	600 V
Insulation resistance	>10 ⁸ Ω
Limiting temperature	-30 ... +90 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	EN 45545-2 Fire protection on railway vehicles
	IEC 61373 Category 1 Class B
	IEC 60664-1
	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
	Please contact your local HARTING subsidiary for further information.



Pushing Performance
Since 1945

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	13.9 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140185494
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522