



Connectors > PCB Connectors > PCB Headers & Receptacles > DYNAMIC 5000 HDR ASSY



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Horizontal**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Number of Rows: **2**

[All DYNAMIC 5000 HDR ASSY \(59\)](#)

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Horizontal
Number of Positions	4
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Base Material	Copper Alloy
Contact Mating Area Plating Material Thickness	.38 µm[15 µin]
Contact Mating Area Plating Material	Gold (Au)



Contact Type	Pin
Contact Current Rating (Max)	45 A

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Mating Retention	With
PCB Mount Retention Type	Retention Leg
Mating Alignment Type	Keyed
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Glass-Filled Thermoplastic
Centerline (Pitch)	10.16 mm [.4 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	15
Packaging Method	Box, Tube

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 3-917807-2
DYNAMIC D-5200M REC HSG 4P X-Y

Also in the Series | Dynamic 5000 Series

Connector Caps & Covers(2)


Connector Contacts(43)

Connector Hardware(3)

Insertion & Extraction Tools(1)




[PCB Headers & Receptacles\(62\)](#)



[PCB Terminal Blocks\(3\)](#)



[Rectangular Power Connectors\(80\)](#)



[Wire-to-Board Headers & Receptacles \(62\)](#)

Customers Also Bought



TE Part #103956-3
[5X4 MTE RCPT SR LATCH .100CL](#)



TE Part #2-917809-2
[DYNAMIC D-5 TAB HSG D/R 4P Y-Y](#)



TE Part #2108965-1
[FPC ANT, MHF, 50mm, UWB 6~8.5 GHz](#)




TE Part #172211-4
[EIS CAP HSG FREE HANG 4P NATUTURAL](#)



TE Part #2271041-1
[0.8FH,R19H.5,040,30/SN,TR,SC](#)




TE Part #170204-2
[EIS CONTACT](#)



TE Part #178326-5
[DYNAMIC DBL ROW HDR ASSY 12P V](#)



TE Part #CAT-HPCH5372
[High Pin Count Header](#)



TE Part #1-1473193-3
[025/040 CAP HSG ASSY 70P](#)

Documents

Product Drawings

[DYNAMIC D-5 HDR H ASSY 4P XY](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1123309-2_D.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_3-1123309-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1123309-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Agency Approvals

[TUV Certificate](#)

English