

11116
Abrasive shaft-mounted wheels, abrasive pink corundum grains, ceramic bonded, ogive-shaped
EN 12413

For universal use

shaft Ø 6 x 40 mm

	art.	Ø mm	h mm	max. rpm Lo=13 mm	
111160010	11116 10X20	10	20	86.600	AR60P5V
111160018	11116 18X30	18	30	43.000	AR46P5V
111160020	11116 20X50	20	50	22.500	AR36/46P5V

