

## Test adapter - PAI-4-FIX BU - 3032729

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test adapter, for 4 mm test plug and terminal blocks with 8.2 mm pitch, color: blue

### Your advantages

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 280303
GTIN	4046356280303
Weight per Piece (excluding packing)	2.380 g
Custom tariff number	85366990
Country of origin	Poland

### Technical data

#### Dimensions

Height	51.5 mm
Length	5.8 mm
Width	5.8 mm
Diameter	5.8 mm
Pin diameter	2.4 mm

#### General

Note	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in
	Do not plug in while the power is connected

# Test adapter - PAI-4-FIX BU - 3032729

## Technical data

### General

	Latching testing accessories, therefore only suitable for being plugged in once
Color	blue

Material	Copper
Ambient temperature (operation)	-40 °C ... 125 °C
Max. voltage	250 V
Maximum load current	10 A
Insertion/withdrawal cycles	1

### Standards and Regulations

Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27440313
eCl@ss 8.0	27440313
eCl@ss 9.0	27440313

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002255
ETIM 6.0	EC002255

### UNSPSC

UNSPSC 6.01	30211812
-------------	----------

# Test adapter - PAI-4-FIX BU - 3032729

## Classifications

### UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121410

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		EAC-Zulassung
-----	---	---------------

---