

## **FEATURES**

- Using oxygen recombination technology
- PbCaSn alloy for plate grids-less gassing, less selfdischarging
- High-quality AGM separator
- High purity raw material
- Silver-coated copper terminals (T1, T2 terminal)
- ABS material

# RS PRO Lead Acid Battery 12V, 20Ah

RS Stock No.: 727-0391



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



**Product Description** 

RS PRO Lead acid batteries are suitable for use across a number of industries as well as for general purpose. They are sealed and have many uses, and are ideal for standby & float applications. These batteries are long life rechargeable batteries.

727-0382 - 6V, 7Ah 727-0385 - 6V, 3.2Ah 727-0388 - 6V, 1.2Ah 727-0391 - 12V, 20Ah 727-0394 - 12V, 35Ah 727-0398 - 12V, 100Ah 727-0401 - 12V, 120Ah 727-0408 - 12V, 55Ah

#### **General Specifications**

Technology	AGM
<b>Designed for Cyclic Application</b>	No
Eurobat Classification	3 to 5 Years,
Container Material	A.B.S. (UL94-HB) conform
Application	Standby & Float applications

#### **Electrical Specifications**

Capacity	20Ah
Nominal Voltage	12V
Terminal Type	T12



### **Mechanical Specifications**

Dimensions	181.5mm x 77mm x 167.5mm
Height	181.5mm
Length	77mm
Width	167.5mm
Weight	5.8kg

Operation Environment Specifications	
Operating Temperature Range	-15 → +50°C

Approvals	
Compliance/Certifications	UL94-HB



## Lead Acid Batteries



