

Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and Silver

RS PRO Fire Sleeve Yellow 5m

RS Stock No.: 0733629



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

General Specifications

Part Number	Ordering Size (mm)
0731335	4
0731176	6
0731177	8
0731178	10
0731179	12
0731180	14
0731181	16
0731182	19
0731183	22
0731184	25
0731185	28
0731186	32
0731187	35
0731188	38
0761153	41
0761154	44
0761155	51
0761156	57
0761157	63
0761158	70
0761160	76
0733626	83
0733627	89
0733628	95
0733629	102
0733630	114
0733631	127
0733632	140
0733634	168
0733635	180
0733636	203

Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2