

/ SUXXEED OFFROAD //



100 %
METAL
FREE



SUXXEED OFFROAD S3 HIGH

Art. Nr. SAP: 62733

Art. Nr.: 6261601

EN ISO 20345: 2011 - S3 CI SRC

Sizes: 36 - 48

APPLICATIONS //

outdoor work, building and construction, general industry, energy, logistic, maintenance, utilities, damp working conditions

TECHNICAL SPECIFICATIONS //

sole: PU2D, excellent grip, oil, hydrocarbon and chemical resistant, self-cleaning sole profile, excellent shock absorption. Injection molded PU scuff cap

upper: water-resistant brown oiled grain leather, microfiber insert, water-resistant tongue and collar, reflective elements, non-metallic eyelets and hooks

lining: 3D mesh, excellent breathability, quick drying

toe cap: metal free

penetration resistant midsole: metal free

hygienic insole: anatomically shaped hygienic insole with EVA heel shock absorber

weight: 640 g in size 42