

# EKOE MPI 130G



Sample image

**Order symbol :** EKOE MPI 130G

**EAN :** 6418074321060

**Product nr :** 2538237

**El. number :**

**Description :** Enclosure, PC

- Finland : 3424766
- Denmark : 8212052819
- Sweden : 2507748

**Remarks :** Grey cover

**Including :** Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws. Including plastic mounting plate.

| Dimensions : | Height | Width | Depth |
|--------------|--------|-------|-------|
| mm :         | 280    | 280   | 130   |
| inch :       | 11.02  | 11.02 | 5.12  |

## Materials :

|                   |                      |
|-------------------|----------------------|
| Material :        | Polycarbonate        |
| Base colour :     | RAL_7035             |
| Cover colour :    | RAL 7035 -light grey |
| Gasket material : | Polyurethane         |

## Ratings :

|                                         |                   |
|-----------------------------------------|-------------------|
| Ingress protection (EN 60529):          | IP66/67;          |
| Impact Resistance (EN 62262):           | IK08;             |
| electrical_insulation :                 | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815) : | Yes               |
| UV resistance :                         | UL 746C           |
| Flammability Rating :                   | UL 94 V0          |
| Glow Wire Test (IEC 695-2-1) °C :       | 960C              |

## Temperatures :

|                               |             |
|-------------------------------|-------------|
| Temperature °C (continuous) : | -40 ... 80  |
| Temperature °F (continuous) : | -40 ... 175 |