ATV21HD30M3X

AC Drive, 117.0A, 40HP, Altivar 21, Type: ATV21, Variable Torque

Technical Characteristics

Frame Size	Size 6A
Horsepower Rating	40HP
Enclosure Rating	Open
Degree of Protection	IP20
Motor Power Rating	30kW
Application	Variable Torque
Ampere Rating	117.0A
Conformal Coating	No
Embedded Communication	Modbus
Integrated EMC Filter	Purchase Separately
Input Phase	3-Phase
Input Voltage	208/240VAC
Output Voltage	Maximum output voltage equal to input voltage
Marketing Trade Name	Altivar 21
Output Phase	3-Phase
Туре	ATV21

Shipping and Ordering

emphing and evening	
Category	22156 -
Discount Schedule	CP4B
Article Number	785901663249
Package Quantity	1
Weight	119 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Υ

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 06/07/2009 10:51:09

