

## Screwdriver - SF-SL 1,0X5,5-150 - 1212552

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver, bladed (lasered), size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip

The figure shows the SZF 1 version

### Why buy this product

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head
- Individually tested safety screwdrivers according to DIN EN 60900 (VDE 0682-201)
- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 589871
Weight per Piece (excluding packing)	83.6 g
Custom tariff number	82054000
Country of origin	Czech Republic

### Technical data

#### Dimensions

Length (b)	248 mm
Width (a)	33 mm
Blade thickness	1 mm
Blade width	5.5 mm
Blade height	150 mm

#### General

Type	Bladed
	Straight
Material	Alloyed tool steel

# Screwdriver - SF-SL 1,0X5,5-150 - 1212552

## Technical data

### General

Test standard	DIN/ISO 2380-1
---------------	----------------

## Classifications

### eCl@ss

eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401
eCl@ss 6.0	21040401
eCl@ss 7.0	21040409

### ETIM

ETIM 4.0	EC000158
ETIM 5.0	EC000158

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## Drawings

### Pictogram

