

Coaxial cables

Coaxial cables



Safety leads with 50 Ω impedance, length 1 m- IEC 61010-2-031 Cat. III 500 V, black:
insulated male BNC / banana plugs with rear connection

> AG1066-Z (2 p)



Safety leads with 50 Ω impedance,
length 1 m IEC61010-2-031 - 600 V CAT III, black

> HX0106 (2 p)



Earth safety leads, length 2 m, Ø 4 mm banana connection
- IEC 61010-2-031 Cat. III 1,000 V:
Female banana plug / female, yellow/green (earth)

> P01295073A (5 p)

Accessories



Set of 2 adapters
Insulated male BNC plug - insulated female plugs (R/B) Ø 4 mm with 19 mm spacing
600 V CAT III

> HX0107



Set of 2 adapters
Insulated female BNC - Insulated plugs (RIN) Ø 4 mm with 19 mm spacing - 600 V CAT III

> P01102101Z



Set of 2 adapters
Male BNC -insulated female sockets (R/B) Ø 4 mm with 19 mm spacing
500 V CAT I, 150 V CAT III

> P01101846



Set of 2 adapters
Male BNC - insulated male sockets (R/B) Ø 4 mm with 19 mm spacing
500 V CAT I, 150 V CAT III

> P01101847



Load adapter
50 Ω BNC additional load

> PA4119-50 (1 p)



Rack for safety leads (1 rack)
Rack for hanging 60 leads

> P01101914 (1 p)

Insulated T-joint IEC 61010-2-031 - 500 V CAT I
1 insulated male BNC / 2 female BNC

> HA2004-Z (3 p)



Insulated extension IEC 61010-2-031 - 500 V CAT I
Female BNC / female BNC

> HA2005 (1 p)



Safety coupling jumper with 19 mm spacing - Ø 4 mm - 36 A
- IEC 61010-2-031:
Set of 10 black coupling jumpers

> P01101892A