

**S.306-200DSLS 306D.SLS - Click wrenches without accessories****Description :**

- Tool equipped with a FACOM SLS attachment solution, preventing any risk of accidental falls.
- FACOM has adopted the clevis solution for particularly heavy and/or large tools (32 - 41 mm wrenches).
- Factory accuracy:  $\pm 2\%$  except: R.306-25DSLS.
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Use possible with accessories:
  - End fitting: 9 x 12 or 14 x 18 mm.
  - Diameter: 30 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Supplied in plastic box.

---

**L [mm]:** 515

---

**Attachment:** 14 x 18

---

**Box:** BP.D3

---

**Capacity [N.m]:** 40 - 200

---

**Graduation [N.m]:** 1,00

---

**[kg]:** 1,300

---