

99 14 300

High Leverage Concreters' Nipper high lever transmission



- 25 % less effort required compared to conventional concreters' nippers of the same size
- Extra-slim form for tying deep mounted steel rods
- To lace concrete reinforcing steel with binding wire from a roll
- Wire is twisted and cut in a single pass
- High-leverage joint, minimising strain, even when thick binding wires are used
- The high damping of the cutting stroke on cutting through the binding wire reduces the strain on tendons and muscles
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

Article No.	99 14 300
EAN	4003773600671
Pliers	bright zinc plated
Head	
Handles	
Cutting capacities hard wire (diameter) Ø mm	2,0
Cutting capacities medium hard wire (diameter) Ø mm	3,8
Head width mm	25,0
Length mm	300
Net weight g	499

technical change and errors excepted

