LEDLENSER SEO3 Head Lamp

See and be seen with this affordable, hands-free LED headlamp for style-conscious outdoor enthusiasts. Weighing only 105g and with two-tone styling for cross-gender appeal, it has a smart silver focusing ring and washable elastic headband made from hypo-allergenic fabric for maximum comfort over prolonged periods. The headlamp itself includes one bright white Cree LED for optimum night-time illumination plus one glare-free red LED to protect night vision. The glow-in-the-dark housing allows wearers to be seen in the dark – a helpful safety feature for runners, walkers and campers. It can be tilted forwards and down within an angle of 90 degrees to make it easier to view and assess any surface or terrain. Ledlenser's patented Advanced Focus System beams consistent white light all the way from flood to spot, lighting up to 100 metres in front with a burn time of 40 hours and 100 lumens brightness. Powered by three AAA batteries it features three of Ledlenser's innovative Smart Light Technology settings: Power, Low Power and Signal, giving the user powerful, practical and safe light options for different situations. A useful switch lock prevents auto-operation in transit and it is waterproof up to IPX4 level. Supplied with 3 x AAA batteries, washable headband and belt-hook.

As a leading international brand of hand-held torches and head lamps, Ledlenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class- leading lighting instruments, Ledlenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. Ledlenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- 1 x CREE Power LED Light Chip
- 1 x Glare-free High End Red LED Light to protect night vision
- Advanced Focus System (AFS) - Flood Beam to Sharply Focused Spot Beam
- Smart Light Technology (SLT) – Power, Low Power, Signal
- Directional Lighting - Lamp Head swivels within an angle of 90 degrees
- Washable, replaceable, anti-allergic headband colour-coded to match lamp head
- Transport Lock – prevents light accidentally switching or
- Lightweight – ideal for extended duration use
- Casing glows when in use – see and be seen
- IPX6 – superior dust and water protection
- Supplied with: Belt Hook and 3xAAA batteries



Technical Information

SEO3	BOOST	POWER	LOW POWER
POWER	x	100 lumens	15 lumens
BEAM DISTANCE	x	100 metres	30 metres
RUN TIME	x	10 hours	40 hours
SIZE	x	WEIGHT	96g
Supplied with : Belt Hook and Duracell® batteries (3xAAA)			

Code	Packaging	Barcode
6103 Green	Test-It	4029113610353