

FEATURES

- **Sintered Bronze Material:** Provides excellent durability and resistance to wear.
- **Flanged Design:** Offers easy installation and secure positioning in assemblies.
- **Dynamic Load Rating of 14 N/mm²:** Ensures reliable performance under dynamic conditions.
- **Static Load Rating of 50 N/mm²:** Supports high static loads, enhancing stability.
- **0.62 in Bore Size:** Suitable for a wide range of shaft diameters.
- **0.87 in Outside Diameter:** Compatible with standard housing dimensions.

RS PRO 0.62 in Flanged Plain Bearing

RS Stock No: 528-229



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 0.62 in Flanged Plain Bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, this bearing is ideal for reducing friction and wear in various mechanical systems, ensuring longevity and performance.

General Specifications

Bore Size	0.62 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.87 in
Width	3/4 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

