



Item no.: 256-402
 Product description: PCB TERMINAL STRIP 2 SOLDER PINS / POLE 2 POLE PIN
 SPACING 5/5.08 MM / 0.2 IN



Produkt kann von Bild abweichen / product may differ

Packing unit 400 4*100 pieces

Product group	4 (Printed Circuit)
Weight	2.03 g
Color	gray
No. of connection Points	2
No. of potentials	2
pole count	2
Height	18.2 mm
Height	0.72 in
Width	12.9 mm
Width	0.508 in
Depth	17.6 mm
Depth	0.693 in
Pin spacing from	5 mm
Pin spacing up to	5.08 mm
Pin spacing from	0.197 in
Pin spacing up to	0.2 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV
Current intensity EN	24 A

Pollution degree
Measured voltage EN

2
630 V



Measured shock voltage	4 kV
Current intensity EN	24 A
Connection method	CAGE CLAMP® CONNECTION
Cross section [mm ²]	0.08 - 2.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [mm ²]	0.25 - 1.5 mm ²
Cross section [AWG]	28 - 12 AWG
Strip length from	5 mm
Strip length to	6 mm
Material group	I
xxx-xxx/000-005	red
xxx-xxx/000-006	blue
xxx-xxx/000-008	dark gray
xxx-xxx/000-009	light gray
xxx-xxx/000-012	orange
xxx-xxx/000-017	light green
xxx-xxx/332-000	with 5,5 mm long solder pins
xxx-xxx/332-xxx	with 5,5 mm long solder pins



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
256-402	ABS	04-HG469925/1-PDA	500/250	16	0,5-2,5
256-402	BV	11915/A0	500/250	16	0,08-2,5
256-402	CCA	NL6249	250	24	0,08-2,5
256-402	CSA	18677-45	300/600	15/5	28-12
256-402	DNV	E-9215	500/250	16	0,08-2,5
256-402	GL	17296-00HH	500/250	16	0,5-2,5
256-402	KEMA	2110204.03	250	16	0,5-2,5
256-402	RMR	11130002	250	16	0,5-2,5
256-402	UR	E45172	300/300	15/10	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected