

Lawn Mower XGT®

LM001G

Model LM001G is a 480mm (18-7/8") cordless lawn mower powered by 40Vmax XGT® Li-Ion battery (two in parallel).

This model features increased convenience, such as automatic switching from one battery to the other battery connected in parallel. Other features and benefits are: Steel cutting deck, Three cutting modes: Normal, Soft no-load, Noise reduction, Rigid handle foldable without tool, Equipped with self-propelled function.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	2500 - 3200 min ⁻¹
Cutting height positions	10
Width of Mowing Deck	48 cm
Mowing Height	20 - 100 mm
Steel Mowing Deck	✓
Rear Wheel Diameter	23 cm
Front Wheel Diameter	23 cm
RPM (Normal mode)	3200 min ⁻¹
RPM (Soft no load mode)	2500 - 3200 min ⁻¹
RPM (noise reduction mode)	2500 min ⁻¹
Actual mowing area 8.0 Ah x 2	2100 - 2600 m ²

User benefits

- Battery protection circuit protects against overloading, over-discharging and over-heating
- Self-propelled for reduce operator fatigue
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing