

270204010

Beluga 220, closed

Beluga 220, closed

Catalogues | Assembly instructions | Declaration of Conformity | Drawing | 3D Data

Technical data

Height	220 mm
Width	116 mm
Depth	51 mm
Material	Polyamide 6 (PA6)
Colour	black-grey (RAL 7021)
Ingress protection	IP65
Degree of protection norm	EN 60529
temperature min.	-40 °C
temperature max.	60 °C
Seal material	CR-(Chloroprene)
Surface resistance	10^12 Ohm
Surface resistance norm	IEC 60093
Other versions on request	EMV

Commercial data

Country of origin	RO
Order unit	1 Piece
Customs tarif number	39269097
Weight	0.247 kg
GTIN	4250157916990

ETIM classification

ETIM 8	EC001031

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

Zubehör - s. Zeichnung
Accessories - see drawing

270200800
Beluga 180/220 Hook set without magnet

Zubehör - s. Zeichnung
Accessories - see drawing

270200810
Beluga 180/220 Hook set with magnet

270200820
Beluga 180/220 Screw set

Zubehör - s. Zeichnung
Accessories - see drawing

270200850
Beluga 180/230 Battery box

Zubehör - s. Zeichnung
Accessories - see drawing

270200860
Beluga Holder for Battery box (4 Mignon

Zubehör - s. Zeichnung
Accessories - see drawing

270200870
Beluga Holder for Battery box (9V Block