

3531 // NYLOFLEX FOAM

Assembly gloves
PPE risk category II



100% recycled polyester
Very slip resistant
Very abrasion-resistant

3531 // NYLOFLEX FOAM



Material:	Polyester, white
Coating:	Nitrile foam, grey
Size(s):	7-11
Packaging unit:	144 pair(s)
Certification:	EN 388, EN 407

NITRAS NYLOFLEX FOAM, assembly gloves, white, nitrile coating, grey (colour code: 1112), partly coated on palm and fingertips, knitted cuff, NITRAS NOW, touchscreen compatible, protection against contact heat (100°C, 15 seconds), particularly sensitive, perfect for working with small parts, very non-slip, perfect grip, very abrasion-resistant, PPE risk category II



EN ISO 21420



Size	7	8	9	10	11
Colour coding system					

Industries

-  Craft
-  Building / Construction
-  Automotive manufacturing
-  Commissioning / shipping
-  Landscape gardening

Advantages

- + 100% recycled polyester
- + Very slip resistant
- + Very abrasion-resistant



Performance values

EN 388:2016 + A1:2018	Test parameter	Performance levels	Test result
 4121A	Abrasion resistance	1-4	4
	Blade cut resistance (Coupe-Test)	1-5	1
	Tear resistance	1-4	2
	Puncture resistance	1-4	1
	Blade cut resistance (TDM)	A-F	A
EN 407:2020	Test parameter	Performance levels	Test result
 X1XXXX	Resistance to flammability	1-4	X
	Contact heat resistance	1-4	1
	Convective heat resistance	1-4	X
	Radiant heat resistance	1-4	X
	Resistance to small splashes of molten metal	1-4	X
	Resistance to large quantities of molten metal	1-4	X
EN ISO 21420:2020 + A1:2024	Test parameter	Performance levels	Test result
	Dexterity	1-5	5

Additional information

	Material	Colour
Palm	Nitrile, sanded, on polyester, partially recycled	grey
Index finger and thumb	Nitrile, sanded, on polyester, partially recycled	grey
Back of the hand	Polyester, partially recycled	white
Fingertips	Nitrile, sanded, on polyester, partially recycled	grey
Cuff / knitted wrist	Polyester, partially recycled	white

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
7	4059904229297	4059904229280	0,46 m	0,37 m	0,24 m	8,5 kg	36
8	4059904229310	4059904229303	0,46 m	0,37 m	0,24 m	8,5 kg	36
9	4059904229334	4059904229327	0,46 m	0,37 m	0,24 m	8,5 kg	36
10	4059904229358	4059904229341	0,46 m	0,37 m	0,24 m	8,5 kg	36
11	4059904229372	4059904229365	0,46 m	0,37 m	0,24 m	8,5 kg	36

Customs tariff number: 61161020910

Country of origin: China