

Slide Compound Mitre Saw XGT®

LS002G

40V max • 216 mm • 4 800 min⁻¹

Efficient brushless cordless saw with a remote start for dust extraction (AWS) for demanding use

Powered by XGT® 40V max battery this brushless saw is extremely powerful. Equipped with single sliding system and rail-forward design enables saw to be placed against wall for maximising work space. Max cutting capacity (90 degrees) 70 x 312 mm. Twin led lights illuminate the working area.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Max. kerf thickness of the saw blade	2,4 mm
Brushless Motor	✓
Capacity 90°	70 x 312 mm
No load speed	4800 min ⁻¹
Capacity 45° left	50 x 312 mm
Max. Bevel Range (Left)	48 / 48 °
Max. Mitre Range (Left)	60 / 60 °
Sound Power Level (L _{WA})	100 dB(A)
Sound Pressure Level (L _{pA})	89 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	16,4 - 17,6 kg
Product Dimensions (L x W x H):	702 x 551 x 557 mm
Capacity 45°	70 x 220 mm

User benefits

- Brushless maintenance-free and long-life motor
- High precision cutting
- Rail-forward design enables to be placed against a wall for maximising work space
- Single sliding system enables smooth operation to produce superior cuts
- Large bevel lock lever; Easy to operate even if the machine is placed close to the wall, because you do not need to reach for the rear of the machine to turn the lever
- Precision Mitre angle adjustment; Can be achieved simply by turning a knob on the turn base
- Extendable sub tables help stabilise long material cuts
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Front knob for easy bevel angle adjustment
- One touch slide lock; Can be easily locked/unlocked by inserting/removing the lock pin
- Ergonomic rubberised D-handle design for better fit and added comfort

Link to product - www.makitauk.com



Related products

Optional AC

B-32839

Circular Saw Blade, Makblade, TCT,



E-06987

Circular Saw Blade, Efficut, TCT,



E-08903

Circular Saw Blade, Efficut T.C.T, 216



E-08919

Circular Saw Blade, Efficut, T.C.T,



Other

User manual

Parts drawing