

RS PRO Professional Workbench

RS Stock No.: 800806, 800807, 800808

Features

- Heavy-duty steel construction
- Durable 24 mm HEXA worktop
- Ergonomic manual height adjustment
- Integrated storage container
- Maximum load capacity: 350 kg
- Large 2000 × 880 mm working area
- Ideal for industrial, assembly, maintenance, and workshop applications



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RRS PRO Heavy-Duty Adjustable Workbench

Maximise productivity with the RS PRO H-Type Workbench Set, a robust and versatile workstation designed for demanding industrial, manufacturing, assembly, and maintenance environments. Featuring a durable 24 mm HEXA worktop, integrated storage container, and a practical vertical upright for mounting accessories, this workbench delivers the perfect combination of strength, organisation, and flexibility. With a 350 kg load capacity, the heavy-duty steel construction provides exceptional stability for tools, equipment, and components, while the manual height adjustment allows users to create an ergonomic working position tailored to their needs. The integrated storage solutions help keep essential items close at hand, reducing clutter and improving workflow efficiency.

Whether used in workshops, production facilities, laboratories, or maintenance departments, the RS PRO Workbench Set is built to withstand everyday industrial use while creating a more organised, comfortable, and productive workspace

General Specifications

Brand	RS PRO
Features	HEXA Worktop Surface
Width	2000mm
Length	880mm
Height	850mm
Type	Workbench
Maximum Load	350kg
Materials	Steel
Colour	Grey

Available Options:

Stock No.	Product Name	Width	Depth	Height
800806	RS PRO Workbench	2000	880	850
800807	RS PRO Workbench with container	2000	880	850
800808	RS PRO Workbench with mobile storage containers, back wall, PDU (Shuko) and LED Lighting	200	880	850

Compatible accessories:

COMPATIBLE PARTS:


FRAME FOR PERFORATED BACK PANEL:

ESD HIGH VERTICAL UPRIGHT (FRAME), 1980x1800mm	800775
ESD LOW VERTICAL UPRIGHT (FRAME), 1980x1800mm	800773
ESD MEDIUM VERTICAL UPRIGHT (FRAME), 1980x1800mm	800774
ESD MIDDLE VERTICAL UPRIGHT, 40x1800mm	800776



PERFORATED BACK PANEL

FULL WIDTH LOW, 2000x300mm	800839
FULL WIDTH HIGH, 2000x600mm	800840
1/2 WIDTH LOW, 900x300mm	800846
1/2 WIDTH HIGH, 900x600mm	800847



SHELVES

ESD 1/2 WIDTH SHELF, 550X300, ADJUSTABLE	800879
ESD 1/2 WIDTH SHELF, 590X300, FIX	800880
ESD 1/2 WIDTH SHELF, 590X400, FIX	800881
ESD 1/2 WIDTH SHELF, 650X300, ADJUSTABLE	800883
ESD 1/2 WIDTH SHELF, 740X300, FIX	800884
ESD 1/2 WIDTH SHELF, 740X400, FIX	800885
ESD 1/2 WIDTH SHELF, 850X300, ADJUSTABLE	800504
ESD 1/2 WIDTH SHELF, 890X300, FIX	800505
ESD 1/2 WIDTH SHELF, 890X400, FIX	800506
ESD 1/2 WIDTH SHELF, 950X300, ADJUSTABLE	800861
ESD 1/2 WIDTH SHELF, 990X300, FIX	800862
ESD 1/2 WIDTH SHELF, 990X400, FIX	800863
ESD FULL WIDTH SHELF, 1140X300, ADJUSTABLE	800864
ESD FULL WIDTH SHELF, 1180X300, FIX	800865
ESD FULL WIDTH SHELF, 1180X400, FIX	800867
ESD FULL WIDTH SHELF, 1440X300, ADJUSTABLE	800868
ESD FULL WIDTH SHELF, 1480X300, FIX	800869
ESD FULL WIDTH SHELF, 1480X400, FIX	800870



ESD FULL WIDTH SHELF, 1740X300, ADJUSTABLE	800871
ESD FULL WIDTH SHELF, 1780X300, FIX	800873
ESD FULL WIDTH SHELF, 1780X400, FIX	800874
ESD FULL WIDTH SHELF, 1940X300, ADJUSTABLE	800875
ESD FULL WIDTH SHELF, 1980X300, FIX	800876
ESD FULL WIDTH SHELF, 1980X400, FIX	800877
ESD KEYBOARD SHELF, 500X351	800878
ESD KEYBOARD SHELF, 700X351	800882
ESD ANGLED KEYBOARD SHELF, 230X330	800508

LIGHT HOLDERS

ESD LIGHT HOLDER 1150X340	800719
ESD LIGHT HOLDER 1450X340	800720
ESD LIGHT HOLDER (INCL. FRAME WITH RAILS for Tool Balancer- 800795)	800722
ESD LIGHT HOLDER (INCL. FRAME WITH RAILS for Tool Balancer- 800795)	800723



LED LIGHTS

LED LAMP 1200MM	800724
LED LAMP 1800MM	800725
LED LAMP 2000MM	800726
LED LAMP 600MM	800727



SUSPENDED DRAWER UNIT

ESD SUSPENDED DRAWER UNIT WITH 1 LOCKABLE	800685
ESD SUSPENDED DRAWER UNIT WITH 1 LOCKABLE DRAWER – Silent Closing	800687
ESD SUSPENDED DRAWER UNIT WITH 2 LOCKABLE	800688
ESD SUSPENDED DRAWER UNIT WITH 2 LOCKABLE DRAWER – Silent Closing	800689
ESD SUSPENDED DRAWER UNIT WITH 3 LOCKABLE	800690
ESD SUSPENDED DRAWER UNIT WITH 3 LOCKABLE DRAWER – Silent Closing	800691



BIN RAIL / COMPARTMENT BOX HANGER


ESD 1/2 WIDTH BIN RAIL – 1000MM	800785
ESD 1/2 WIDTH BIN RAIL - 600MM	800791
ESD 1/2 WIDTH BIN RAIL – 750MM	800792
ESD 1/2 WIDTH BIN RAIL – 900MM	800794
ESD FULL WIDTH BIN RAIL – 1200MM	800786



ESD FULL WIDTH BIN RAIL - 1500MM	800788
ESD FULL WIDTH BIN RAIL - 1800MM	800789
ESD FULL WIDTH BIN RAIL - 2000MM	800790


ACCESSORIES

ESD FOOTREST 604X360	800693
ESD MONITOR HOLDER FOR LCD, 55X120	800728
ESD PC HOLDER, 225X463	800829
ESD TOOL BALANCER CART, 60X52	800795
ESD BRAKE FOR CART, DIAMETER 25MM	800667
ESD ANGLED DOCUMENT HOLDER	800684



WIRE HOLDERS

ESD FULL WIDTH WIRES HOLDER, 1000X150	800777
ESD FULL WIDTH WIRES HOLDER, 1300X150	800778
ESD FULL WIDTH WIRES HOLDER, 1600X150	800779
ESD FULL WIDTH WIRES HOLDER, 1800X150	800780
ESD 1/2 WIDTH WIRES HOLDER, 450X150	800781
ESD 1/2 WIDTH WIRES HOLDER, 600X150	800782
ESD 1/2 WIDTH WIRES HOLDER, 750X150	800783
ESD 1/2 WIDTH WIRES HOLDER, 850X150	800784



POWER DISTRIBUTION UNITS

POWER STRIP FULL WIDTH, 1900X100, 6 sockets	FRENCH	800732
POWER STRIP FULL WIDTH, 1900X100 8 sockets	SCHUKO	800733
POWER STRIP FULL WIDTH, 1900X100, 6 sockets	FRENCH	800734
POWER STRIP FULL WIDTH, 1900X100, 8 sockets	SCHUKO	800735

