



Datasheet

RS PRO IP66 MONOBLOCK INDUSTRIAL ENCLOSURE

Glass Reinforced Polyester (GRP)

H:800 × W:600 × D:300mm

Stock number: 1927121

EN



Feature

- Manufactured from fibre glass reinforced polyester, moulded by hot compression.
- Colour Light Grey RAL 7035
- Self-extinguishable: 960°C test withstand. Halogen free. Double insulation. No electrical contact risks.
- Degree of protection IP66 UNE 20324 (EN 60529).
- Certification of compliance with IEC62208 enclosure standard. Suitable for indoor or outdoor use.
- Large door opening (180°). Reversibility for installation right or left door opening.
- Anti-intruder hinges system.
- Other lock options available
- Galvanised steel mounting plate.
- Resistant to harsh atmospheres.
- Light weight gives an easy installation.
- 10+ years. Long life lasting without maintenance under standard environmental conditions.


Description

Standard enclosure colour light grey RAL 7035 supplied with galvanised steel back plate & direct wall mounting fixings.

Dimensions H:800 × W:600 × D:300mm

Weight 19.05kg

Dimensions



Installation and assembly system				
Inside Installation	Yes	Wall Surface	Yes	
Outdoor Installation	Yes	Floor Mounting	Yes	
Flush Mounting	No	Pole Mounting	Yes	

Enviromental Performance	
Minimum temperature	-30° C
Maximum temperature	70° C
Compression resistance	100kg
IP dust water protection degree IEC-60529	66
IK impact protection degree IEC-62208	10

Electrical Performance			
Nominal tension direct current up to:	1500 VdC		
Nominal tension alternating current up to:	1000 Vac		
Maximum power dissipation ∆T=40℃ (wall surface)	185.0 W		

