

High value tub vacuum cleaner designed for professional cleaners

### Equipment:

- Suction hose 2.5 m
- Metal suction tube, 2 x 0.5 m
- Filter bag Fleece
- Switchable floor nozzle 262 mm
- Antistatic system
- Container material Plastic
- Floor tool

Order no.: 1.527-411.0



### Technical data

Air flow rate (l/s)	61
Vacuum (mbar/kPa)	244/24.4
Container capacity (l)	10
Max. intake performance (W)	1250
Standard nominal size (mm)	32
Length of cord access. (m)	12
Sound level (db(A))	62
Sound power level (db(A))	75
Weight (kg)	6.5
Dimensions (L x W x H) (mm)	355x310x410
Energy efficiency class	E

## Details

### Description

The T 10/1 Adv brings new levels of quality and value to the contract cleaner tub vacuum sector. With key features designed to keep purchase and maintenance costs low, the T 10/1 Adv offers the toughness, simplicity, performance and value contract cleaners demand.

---

### Features & Benefits

Large, round permanent main filter of washable nylon

Extremely strong and dense enough for vacuuming without a filter bag.

Service-friendly

The cord can be replaced quickly and easily by loosening two screws.

---

## Accessories

### Adapter (tube -> nozzle)

#### Adapter

From DN 32 to DN 35: Plastic adapter (electrically non-conductive). Suitable for BV and T vacuum cleaners.



**Order no. 6.902-083.0**

### All-purpose brushes

#### All-purpose brush, DN 32

All-purpose plastic brush Bristles: 120 x 45 mm. For all T and BV types.

**Order no. 6.906-122.0**



### Combi-nozzles (dry)

#### Combination floor tool (dry)

Plastic combination floor tool with changeover function (ID 32; 260 mm), with stainless steel base plate.



**Order no. 6.906-211.0**

#### Combination floor tool for parquet

Plastic combination floor tool for parquet (DN 32) with brush strips and two rollers, suitable for all industrial T vacuum cleaners. Combination floor tool without changeover function. 360 mm



**Order no. 6.906-107.0**

#### Combination floor tool

Plastic combination floor tool with plastic base plate and two rollers.



**Order no. 6.906-812.0**

### Connecting sleeves

#### Adapter, DN 32/35, with internal thread

Electrically non-conductive adapter with internal thread. For connecting two suction hoses without connectors. Suitable for DN 32 or DN 35.



**Order no. 6.902-077.0**

### Crevice nozzles

#### Crevice nozzle

Plastic crevice tool (DN 32) for industrial dry vacuum cleaners for vacuuming in crevices and corners.



**Order no. 6.903-403.0**

## Exhaust air filter

### Motor protection filter felt

Order no. 6.414-611.0



## Extension hoses (Clip-system)

### Extension hose, C 32, C 35 clip system

Electrically non-conductive standard extension hose for all C-32 and C-35 hoses with clip system.

Order no. 6.906-237.0



### Extension hose C 32-, C 35-Clip-system, el.

for all C-32 and C-35 hoses, electrically conductive.

Order no. 6.906-277.0



## Fabric filter bag

### Fabric filter bag

Cotton filter bags, washable up to 40°C, suitable for T7/1, T 10/1 and T 12/1 models.

Order no. 6.904-316.0



## Fleece filter bags (3 ply)

### Fleece filter bags

Extremely tear-resistant, 3-ply fleece filter bags, dust class M. Fleece filter bags have 2 to 3 times the capacity of conventional paper filter bags. Standard for T 10/1 and T 12/1.

Order no. 6.904-315.0



### Fleece filter bags

Fleece filter bag, 3-ply, tear-proof, dust class M, large-scale consumer unit.

Order no. 6.904-321.0



## HEPA filter for dust class H

### ABS HEPA-filter T 191 and T 10/1

HEPA-filter cartridge with montage set for 6.414-634.0

Order no. 2.641-229.0



### HEPA filter cartridge

HEPA filter cartridge, paper / metal (H 13)

Order no. 6.414-634.0



## Main filter baskets

### Main filter basket with reinforced fleece

Plastic frames with reinforced fleece material, washably to 40°C.

Order no. 5.731-649.0



## Nozzle sets

### Nozzle kit ID 32, for T vacuum cleaners with clip holder

Nozzle kit (DN 32) for all industrial dry vacuum cleaners, includes crevice tool, upholstery tool, round brush and clip holder.

Order no. 2.860-143.0



## Paper filter (2 ply)

### Paper filter bags for T 7/1, T 10/1, x10

10 paper filter bags (BIA-C dust class M), suitable for all industrial dry vacuum cleaners (e.g. T 7/1 und T 10/1).

Order no. 6.904-333.0



### Paper filter bags, bulk consumer pack

For bulk consumers: 300 paper filter bags (BIA-C dust class M) suitable for all T 7/1 and T 10/1 industrial dry vacuum cleaners.

Order no. 6.904-337.0



## Plastic bend

### Plastic bend, C-ID 32

Plastic with C-32 clip system.

Order no. 4.408-051.0



### Plastic bend

Electrically conductive plastic bend (DN 32) with C-32 clip system, reduces static buildup. Optional for BV 111, T 7/1, T 191, T 10/1, T 12/1, T 201/T201 + ESB 28.

Order no. 4.408-052.0



### Comfort plastic bend, C-ID 32

Plastic bend (DN 32) with C-32 clip system with opening for adjusting the floor tool for high-pile or extremely dense textile coverings.

Order no. 4.440-865.0



## Radiator brushes

### Radiator brush

Radiator brush is suitable for crevice tool 6.903-403.0

**Order no. 6.903-404.0**



## Repair kits

### Repair set, C 32

Repair set (C32) includes threaded hose adapters for industrial T vacuum cleaners with clip system.

**Order no. 2.639-739.0**



## Suction brushes

### Suction brush

Rotatable suction brush (DN 32 plastic) with PA bristles, 70x45 mm. Only for BV and T vacuum cleaners.

**Order no. 6.903-887.0**



## Suction hoses (Clip-system)

### Suction hose, (clip system), C 32

2.5 m suction hose with dry vacuum cleaner connection, clip connection (C 32).

**Order no. 4.440-911.0**



## Suction hoses complete (Clip-system)

### Suction hose, complete (clip system), C DN 32, 2.5 m

Improved quality: 2.5 m suction hose with dry vacuum cleaner connection, clip connection and bend (C-DN 32).

**Order no. 4.440-907.0**



## Suction tubes metal

### Suction tube

Metal suction tube (DN 32, length 0.5 m) with black plastic coating, suitable as an extension, e.g. vacuuming ceilings.

**Order no. 6.906-618.0**



### Telescopic suction tube

Chromium-plated metal telescopic tube (DN 32, length: 0.61-1 m), suitable as an extension, e.g. vacuuming ceilings.

**Order no. 6.903-524.0**



## Suction tubes metal

### Suction tube

Metal

Order no. 6.903-850.0



## Turbo nozzle

### Turbo nozzle

Plastic turbo upholstery nozzle (DN 35/32, 160 mm) with reduction sleeve.

Order no. 2.860-113.0



### Turbo nozzle, DN 32

Plastic turbo floor nozzle (DN 35/32, 270 mm) with reduction sleeve.

Order no. 2.860-114.0



## Upholstery nozzles

### Upholstery nozzle

Plastic upholstery tool (DN 32) with thread catcher, standard for T 201, T 201 + ESB 28. Optional for T 7/1, T 191, T 10/1.

Order no. 6.903-402.0

