



Plug-in rail H: 1800 mm

Model	
product brand name	SIVACON S4
product designation	plug-in strips
design of the product	without main busbar top
design of the surface	zinc plated
General technical data	
design	assembly kit
RAL color number	other
color	miscellaneous
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	1 800 mm
width	42 mm
depth	40 mm
installation width for cabinet installation	42 mm
installation depth for cabinet installation	40 mm
shape of inner subdivisions	
• shape 2a	No
• shape 2b	No
• shape 3a	No
• shape 3b	No
• shape 4a	No
• shape 4b	No
mounting position	vertical
net weight	4 kg
material	sheet-steel
Certificates	
reference code according to IEC 81346-2	UC
Approvals Certificates	
General Product Approval	other



[Miscellaneous](#)



[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ3000-0BA83>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ3000-0BA83>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ3000-0BA83

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/15/2025 

