



1


2

3


4

Notes: (Unless Otherwise Specified)  
 1. Waterproof Rate: IP68.  
 2. Recommend Panel Thickness: 0.8 to 6.0 mm.  
 3. Recommend Torque: 19~20 Kgf-cm.  
 4. Mating Cap P/N:125-7929  
 5. RoHS Compliant.

REV	ECN#	DESCRIPTION OF REVISION	DRAW BY DATE	CHECK BY DATE	APPROVE BY DATE
A0		Mass Production	Joyce 07/10/14	Lucas 07/10/14	Roy 07/10/14



11	Over Mold	PVC Color: Black	1
10	USB-A Plug	Housing: Thermoplastic, Color: Black Contacts: Copper Alloy, Finish: Au Plated Shell: Cold Roll Steel, Finish: Ni Plated	1
9	Cable	UL2725 1P*28AWG*2C*24AVG*AL/My*3*3 OD=5.0mm, Color: Black	1
8	Metal Washer	SUS Finish: -	1
7	EMI Shielded Plate	Copper Finish: Ni Plated	1
6	Glue	Epoxy Color: Black	
5	PCB	FR-4 Color: Green	1
4	USB-A Receptacle	Housing: Thermoplastic, Color: Black Contacts: Copper Alloy, Finish: Au Plated Shell: Copper Alloy, Finish: Ni Plated	1
3	O-Ring	Silicone Color: Red	1
2	Hex Nut	Zn Alloy Finish: Ni Plated	1
1	Housing	Zn Alloy Finish: Ni Plated	1
Item	Part Name	Material / Finish	Qty



Mating Part:  
122-3029

TITLE										REV.
USB-A Metal C3 Panel Jack Screw + USB-A Plug With Cable										A0
THIRD ANGLE PROJECTION		SIZE	SCALE	DRAW / DATE	CHECK / DATE	APPROVE / DATE	TOLERANCES	UNIT	SHEET	
		B	1:1	Joyce 07/10/14	Lucas 07/10/14	Roy 07/10/14	X.X ± 0.5 X.XX ± 0.2	X.XXX ± 0.05 ANGLES ± 1°	mm	1/1

RS Stock No  
122-3031

1

2

3

4