



8 003910 140523

PACKING	INNER	MASTER
	 pcs	 pcs
Colour box	6	6



TECHNICAL DATA

Name	WIANGROW 20W + TRIPPIEDE
Power supply	220V AC
Power supply provided	YES
Type of power supply provided	INTERNAL DRIVER
Lighting source	2835 SMD LED
Lighting power (W)	20
Electricity consumption (W)	20
Lumen	1800
IRC	70
Light colour	4000K
Light beam	DIFFUSE
LED lifespan (hours)	25000
Beam angle (°)	110°
Power cord length (cm)	300
Cable section	H05RN-F3G1.0
Switch	NO
Functions	ON / OFF
Plug	Type E / F - 2 pin (EU Hybrid)
IP Protection	IP65
Insulation class	I
Dimmability	NO
Color	RED
Material	ALUMINIUM
EPREL code form	2528802
Container product (registered form code)	12006665
Product container (energy class)	F
Eprel PDF file	https://storage.onpage.it/2aad3db35f9776ff82da6673dc10d80dd107f088/Fiche_2528802_EN.pdf
Link db eprel	https://eprel.ec.europa.eu/qr/2528802
Accessories included	Cable
Warranty	2 YEARS
Width (mm)	800
Depth (mm)	140
Height (mm)	100
Net weight (Kg)	2.306

DESCRIPTION

LED spotlight on a tripod. Power: 20W, 1800lm, natural light 4000K. The spotlight contains a non-replaceable class F light source. The lightweight yet sturdy aluminum frame makes it easy to move; it rises to a height of 155cm. The base opens to a diameter of 100cm. 3 meter neoprene cable H05RN-F 3G1 mm² with Schuko socket. Waterproof: IP65; perfect for outdoor use. Suitable for: BBQs, photo shoots, party lighting, construction site lighting, garage lighting, etc.

LOGISTICS DATA

Packing type	Colour box
Pack length (mm)	200
Pack width (mm)	810
Pack height (mm)	170
Packed product weight (kg)	2.909
Inner length (cm)	83
Inner height (cm)	41
Quantity in inner	6
Gross weight inner (kg)	19.000
ITF INNER	18003910140520
Quantity in master	6
How many pieces on 80x120 pallet (pz)	36
INTRASTAT Code	94054210
DEEE	0.25

