

## 1/2" 12-POINT LONG SOCKETS - METRIC | E032203



### Description

- ISO 2725-1 - DIN 3124 - ISO 1174-1 - ISO 1711-1 - ISO 691
- Chrome vanadium steel.
- OGV® profile: tightening torque applied to the sides rather than to the angles of the nut.
- High Chrome finish.
- For manual use.

### Information

<b>EAN</b>	3258950322032
<b>A [mm]</b>	10
<b>d1 [mm]</b>	22
<b>d2 [mm]</b>	15.5
<b>L [mm]</b>	79
<b>L1 [mm]</b>	17
<b>Conditioning</b>	1
<b>[g]</b>	98

