


PHE F60FTBFLG



Size	60
Bushing no.	1610
Nominal torque (Nm)	-
Max torque (Nm)	-
Max speed (r/min)	-
Min. bore (mm)	14
Max. bore (mm)	42
Weight (kg)	0.00052
E (mm)	25