

DCD701D2-QW

12V XR Brushless Sub-Compact Drill Driver - 2 X 2Ah Batteries



5035048709832



Product Description :

The DCD701 12V XR drill driver is designed for precision applications like small pilot holes, but also can handle up to a 20mm drill bit into Timber. Small enough to fit in the tightest places at only 152mm long and enough power to get the job done with 57.5Nm of torque and a 2 speed transmission. It also features a bright LED positioned on the foot to illuminate all work areas.

Product Features and Benefits :

- 12V XR Brushless Drill Driver with Compact Design
- BRUSHLESS MOTOR: Delivers high performance, extends tool life and allows for a much shorter design
- 15-POSITION ADJUSTABLE TORQUE CONTROL: For consistent screwdriving into a variety of materials
- BRIGHT LED ON TOOL FOOT: For high visibility in low light situations
- ULTRA COMPACT, LIGHTWEIGHT DESIGN: Allows use in confined spaces
- TWO SPEED ALL METAL TRANSMISSION: For increased runtime and longer tool life

Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

Product Applications :

All wood drilling tasks up to 20mm ; Screwdriving ; Screwdriving

Included items :

- Belt Hook (x1)
- 2Ah XR Li-Ion Battery Pack With State of Charge Indicator (x2)
- 12/18V XR 2A Charger DCB112 (x1)
- TSTAK Compatible Kitbox (x1)

Technical specifications :

- Max. Drilling Capacity (Wood) [Metric] : 20 mm
- Power : 1800 W
- Max Torque [Metric] : 57.5 Nm
- Battery Capacity : 2.0 Ah
- Battery Voltage : 12 V
- Weight (Including Battery) [Metric] : 19 Kg
- Power Output : 250 W
- Maximum Drilling Diameter [Steel] [Metric] : 10 mm
- Max. Drilling Capacity (Metal) [Metric] : 10 mm
- Maximum Drilling Diameter [Wood] [Metric] : 20 mm
- Max. Cutting Capacity [Wood] [Metric] : 20 mm
- Chuck Capacity [Metric] : 0-10 mm

