



C-170781



ON TAPE 型番	型番	日本国有鉄道仕様書図面	寸法 "H"	寸法 "A"	寸法 "L1"	寸法 "L2"	寸法 "B"	マーキング
2-170781-1	170781-1	ED564465, PS1.25-4	4.4	10.1	16	21	14.1	125-4
—	170781-2	ED564465, PS1.25-5	5.4	11.1	16	21	15.1	125-5

E ADDED ON TAPE ³⁰⁸⁻⁷⁶¹⁰ P/N 05 NO 400/10

D ADDED MATL. FINISH ³⁹⁻¹³¹⁸ 17/ JNK 11/27/79

C ADDED DIM'S ³⁶⁻¹¹⁸⁷ 8.8 MN 8/10

B ADDED MARK ³⁷⁻¹¹⁸⁷ H.S. JIN 8/11/75

A REVISED (REV. A) ³⁸⁻¹¹⁸⁷ J.S. JIN 7/1/75

O ADDED *MARK ³⁹⁻¹¹⁸⁷ P.DWG. J.S. J.S. 7/1/75

O RELEASED ³⁹⁻¹¹⁸⁷ J.S. J.S. 7/1/75

4 LTR 4/11/72 REVISION RECORD DR CHK DATE

CR 4/11/72 DE

CHK 4/11/72 APP

1975 AMP JAPAN LTD. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND ON PATENTS PENDING		参考図面 (CUSTOMER COPY) REFERENCE ONLY	
電気銅		AMP 日本エー・エム・ピー株式会社 TOKYO JAPAN	
電気銅		TRADE MARK	
WIRE RANGE 0.26 ~ 1.04 TYP AWG 22-18		IF CLASS 丸型	
INSULATION DIA		TYPE プラスチ、2'リッブ	
TOLERANCE EXCEPT AS NOTED		SCALE	
1:1		LOC SIZE BY NO	
JAC-170781		E	
総線被覆端子			