

Manifold block VABM-B10-30E-N34-10

Part number: 8026376

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Grid dimension	32 mm
Mounting position	optional
Max. number of valve positions	10
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	5646 g
Type of mounting	With through-hole
Pilot air port 12	1/8 NPT
Pilot air port 14	1/8 NPT
Pneumatic connection, port 1	3/4 NPT
Pneumatic connection, port 3	3/4 NPT
Pneumatic connection, port 5	3/4 NPT
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy