

Datasheet

RS 15 Core Screened Industrial Cable, PVC Sheath, 5.2mm OD, 0.055 mm² CSA 0.25 A, 300 V, 100m

Stock Number - 660-0410



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):300

Flammability Test: IEC60332-1



Construction:

Conductor:Tinned Copper

Conductor Dia. (mm): 0.10±0.008 x 7

Insulation: PVC

Insulation Dia. (mm): 0.7±0.05 x 15C

Tape: Mylar Spiral

Coverage:≥115%

Braid Shield : Tinned Copper

Conductor Dia. (mm): 0.15

Conductor Qty: 16x6

Pitch(mm):

Coverage : 91%

ID Thread : Green, White/Green

A rip cord : 500 D

Jacket: FR-PVC

Outer Dia. (mm): 5.2±0.15

Colour:

The colour of the insulation: Red ,

Blue , Green , Yellow ,

White , Black , Brown , Violet ,

Orange , Pink , Light Green ,

Grey , Red/Blue , Green/Red ,

Yellow/Red

The jacket colour: Black

Marking(3times/m):

RS 6600410 7 - 1 - 15C

Performance:**Electrical Characteristics:**

Max.Conductor DC Resistance at 20°C (Ω /Km) :
<345

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :
>200

Current Rating : 0.25 A

