



PRODUCT DATASHEET

Datasheet creation date: 2025/07/09 7:32 (UTC)



7205BEAT85

Single-Row Angular Contact Ball Bearings

Boundary Dimensions

d	25	mm	Bore diameter
D	52	mm	Outside diameter
B	15	mm	Width
r (min.)	1	mm	Chamfer dimension
r1 (min.)	0.6	mm	Chamfer dimension

Basic Load Ratings

Cr	18400	N	Basic dynamic load rating
C0r	10200	N	Basic static load rating

Speeds

Grease	12000	min-1	Grease lubrication
Oil (Oil-bath)	17000	min-1	Oil-bath lubrication

Dimensions

a	23.7	mm	Effective load center
---	------	----	-----------------------

Abutment and Fillet Dimensions

da (min.)	31	mm	Diameter of shaft abutment
Da (max.)	46	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Mass

Mass approx.	0.127	kg	Mass approx.
--------------	-------	----	--------------

