



## 18V XR Brushless Body Grip Jigsaw – 2 X 5Ah **DCS335P2-QW**

Intelligent variable speed trigger & lock-off switch for quick controlled cuts and enhanced work safety

4-position pendulum action controls the aggressiveness or smoothness of cuts

Tool free adjustable shoe with anti scratch cover bevels to 45 degrees in both directions

Quick and easy keyless blade change system accepts T- shank blades  
Overmoulded soft grip on handle, provides additional user comfort and reduces user fatigue



Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	86 dB(A)
----------------	----------

Uncertainty K 4 (Vibration)	2.2999999999999998 m/s <sup>2</sup>
-----------------------------	-------------------------------------

Uncertainty K 3 (Vibration)	3.6 m/s <sup>2</sup>
-----------------------------	----------------------

Battery Capacity	5 Ah
------------------	------

Power Source	Cordless
--------------	----------