



PRODUCT-DETAILS

UPS PowerValue 11LI Up 600 VA

UPS PowerValue 11LI Up 600 VA



General Information	
Extended Product Type	UPS PowerValue 11LI Up 600 VA
Product ID	4NWP100170R0001
EAN	7640169262609
Catalog Description	UPS PowerValue 11LI Up 600 VA
Long Description	VI UPS PowerValue 11LI Up 600VA/360W:230V:50/60Hz:simulated sinewave:2 min

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	221d0688-aae7-414c-9217-381526c61e7a Switzerland
Simplified SCIP	c6f5ccf4-71fe-418a-a974-19b67efba846 Germany ce3fb638-aaf8-4e0a-9f81-4a0bd8aa35ba Netherlands a021d7c5-cee2-4ad2-bbb4-a52e17eb6feb Spain e6c4e29e-3159-4376-9926-41d46df53b87 Netherlands e504bb93-2b18-4d0a-8c5e-82f9d5b0a141 Germany e157c111-5839-4542-8703-cb5ce78de44b Denmark

51637dd-f1b8-42d2-b695-218ff3b1bc08	Poland
9c84a092-5af6-4bf7-b098-f7e555438e7b	Norway
97edee7c-bf7d-4830-8803-303e740213b7	Finland
98087d92-d78f-4a15-8a7f-41e342795220	Netherlands
4ec9d11a-f107-4a42-ba58-03a21e8d89e4	Germany
29d298b2-f974-4a3f-8022-4fadac902b63	Croatia
4d4bf0ee-8f86-4180-b21d-195847446fb8	Czech Republic
26df521e-3ac6-4047-9c0a-38f384611633	Poland
adb29e63-7cdb-440c-801f-fcf201d06eb2	Netherlands
1d378ca1-10e6-437e-8aeb-b269a4f7032b	Netherlands
391a8928-4250-441d-8ca2-00488f457c75	Estonia
9dd4cd21-ea48-45b8-b95f-bd0236f5402e	Greece
66134fc4-282b-4be2-9188-61af5b84b184	Portugal
bda32812-ba73-4377-8f94-12c90ea2dc6e	Bulgaria
7cb1c10d-93ed-4ee9-9e01-7b2790b15f62	Sweden
44c8a55b-8bcb-4391-8a20-5e9eec4e7a40	France
3880375a-c5e9-4550-bd17-bb4c0a2df909	Sweden
81bbe73c-26f4-488e-83b3-90bf32abd8b2	Poland
4500b888-1892-4cb0-aa3b-3254604ebc7a	Germany
9a8a72b1-6896-4553-9a46-231a6d2835cb	Germany
3cfb7c9e-7ff6-4d97-9379-56028801430a	France

Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Norway)	6600712
Country or Territory of Origin	China

Dimensions

Product Net Width	122 mm
Product Net Height	160 mm
Product Net Depth / Length	315 mm
Product Net Weight	4.1 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	197 mm
Package Level 1 Height	250 mm
Package Level 1 Depth / Length	395 mm
Package Level 1 Gross Weight	5.3 kg
Package Level 1 EAN	7640169262609

Technical	
Apparent Power Output	600 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.1 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U _{in})	230 V
Input Voltage Type	AC
Number of Batteries	1
Number of Outputs	C13 Connection 4
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	360 W

Certificates and Declarations	
Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

External Classifications and Standards	
ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories	
UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V	

