




Retro-reflective sensor

OIP-FBOA



Product characteristics	
Type of light	red light
Housing	threaded type
Application	
Special feature	polarisation filter
Function principle	Retro-reflective sensor
Electrical data	
Operating voltage [V]	20...250 AC/DC
Protection class	II
Reverse polarity protection	no
Type of light	red light
Wave length [nm]	660
Outputs	
Output function	light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC [V]	10.5
Max. voltage drop switching output AC [V]	10.5
Minimum load current [mA]	15
Max. leakage current [mA]	6
Permanent current rating of switching output AC [mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC [mA]	250; (350 (...50 °C))
Short-time current rating of switching output [mA]	2200; (10 ms / 0,5 Hz)
Switching frequency AC [Hz]	25
Switching frequency DC [Hz]	35



Retro-reflective sensor

OIP-FBOA

Short-circuit proof	no
Overload protection	no
Detection zone	
Range referred to prismatic reflector [m]	0.15...2; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Max. light spot diameter [mm]	200
Light spot dimensions refer to	at maximum range
Polarisation filter available	yes
Operating conditions	
Ambient temperature [°C]	-25...60
Protection	IP 65
Tests / approvals	
EMC	EN 60947-5-2
MTTF [years]	310
Mechanical data	
Weight [g]	121
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 125
Thread designation	M30 x 1.5
Materials	PBT; PPO modified
Lens material	PMMA
Displays / operating elements	
Display	switching status 1 x LED, yellow
Electrical connection	
Required protection	miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting
Accessories	
Items supplied	lock nuts: 2 screwdrivers
Remarks	
Remarks	Recommendation: Check the safe functioning of the unit after a short circuit.
Pack quantity	1 pcs.


Retro-reflective sensor

OIP-FBOA

Electrical connection

terminals: ...1.5 mm²; Cable sheath: Ø 7...13 mm; Cable gland: M20 X 1.5

Connection



Note : miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting

Diagrams and graphs

excess gain graph

