## **3M™ Reclosable Fastening Solutions**

			THE TOWN		NATIONAL PROPERTY OF THE PARTY	NAT T	NAT T	NATION OF THE PARTY OF THE PART	NATION OF THE PARTY OF THE PART				ANT T	
Product number	SJ3526	SJ3527	SJ3571	SJ3572	SJ3540	SJ3541	SJ3542	SJ3550CF	SJ3551CF	SJ3552CF	SJ3560	SJ3870	SJ3871	SJ4570
Properties/suitable for	Flexible & bendable	Flexible & bendable	Flexible & bendable	Flexible & bendable	Polypro- pylene & polyethylene	Polypro- pylene & polyethylene	Polypro- pylene & polyethylene	Metals & plastics	Metals & plastics	Metals & plastics	Translucent materials	Powder- coated paints	Powder- coated paints	Thin – Low-profile attachment
Key features (info box)														

Physical and Performand	ce Charact	eristics, Ke	ey Feature	s										
Product number	SJ3526	SJ3527	SJ3571	SJ3572	SJ3540	SJ3541	SJ3542	SJ3550CF	SJ3551CF	SJ3552CF	SJ3560	SJ3870	SJ3871	SJ4570
Engaged thickness	3.6 mm ± 15%	3.6 mm ± 15%	3.6 mm ± 15%	3.6 mm ± 15%	5.7 mm ± 15%	5.7 mm ± 15%	5.7 mm ± 15%	5.7 mm ± 15%	5.7 mm ± 15%	5.7 mm ± 15%	5.7 mm ± 15%	6.1 mm ± 15%	6.1 mm ± 15%	2.31 mm ± 15%
Adhesive type	Rubber	Rubber	Acrylic	Acrylic	Rubber	Rubber	Rubber	White acrylic	White acrylic	White acrylic	Clear acrylic	Modified acrylic	Modified acrylic	Modified acrylic
Colour	Black, white	Black, white	Black, white	Black, white	Black	Black	Black	Black	Black	Black	Translucent	Black	Black	Translucent
Stem density (per cm²)					40	62	26	40	62	26	40	40	62	109
Holding power											Illi			
Temperature resistance	49 °C	49 °C	93 °C	93 °C	49 °C	49 °C	49 °C	93 °C	93 °C	93 °C	104 °C	82 °C	82 °C	70 °C
Surface energy														
High	++	++	++	++	++	++	++	++	++	++	++	++	++	++
Medium	++	++	++	++	++	++	++	+	+	+	+	++	++	++
Low	++	++	-	-	++	++	++	-	-	-	-	-	-	+
Closure cycle life	5.000 x	5.000 x	5.000 x	5.000 x	1.000 x	1.000 x	1.000 x	1.000 x	1.000 x	1.000 x	1.000 x	1.000 x	1.000 x	150 x
Indoor and outdoor use			<b>1</b>	<b>⚠</b> / <b>ॐ</b>				<b>△</b>		<b>1</b>		<b>1</b>		

Suggested Applications														
Product number	SJ3526	SJ3527	SJ3571	SJ3572	SJ3540	SJ3541	SJ3542	SJ3550CF	SJ3551CF	SJ3552CF	SJ3560	SJ3870	SJ3871	SJ4570
Panel and cover plate attachment			•	•	•	•	•	•	•	•	•	•	•	
Interior signage			•	•	•	•	•	•	•	•	•	•	•	
Office partitions			•	•	•	•	•	•	•	•	•	•	•	
Graphic attachment			•	•	•	•	•	•	•	•	•	•	•	
Access panels			•	•	•	•	•	•	•	•	•	•	•	
Specialty vehicles (interior attachments)			•	•	•	•	•	•	•	•	•	•	•	
L-bracket edging, repositionable shelving					•	•	•	•	•	•	•	•	•	
Hang signage			•	•	•	•	•	•	•	•	•	•	•	
Decorative appliance trim attachment			•	•										•
Light-weight access panels			•	•										•
Point of purchase display and signage	•	•	•	•										•
Securing fabric to furniture cushions	•	•												
Construct composite assemblies	•	•	•	•										
Attach cushioning panels	•	•	•	•										
Hang graphics and banners that change frequently	•	•	•	•										
Attach removable seat cushions	•	•	•	•										
Product number	SJ3526	SJ3527	SJ3571	SJ3572	SJ3540	SJ3541	SJ3542	SJ3550CF	SJ3551CF	SJ3552CF	SJ3560	SJ3870	SJ3871	SJ4570

## **Product Use**

All statements, technical information, and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluates the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.