


LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				S	REVISED PER 0L20-0147-97	18JUL97	OK MJ5




METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
8 AWG SOLID OR STRANDED	8 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
8 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 8* APPROX AS SHOWN



50	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	LOOSE PIECE BOX 33460	8-33460-2
----	UNPLATED	LOOSE PIECE	2-33460-4
1000	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	33460 TAPE MOUNTED ON 30.48[1.200] CENTERS	2-33460-3
1500	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	33460 TAPE MOUNTED ON 15.24[.600] CENTERS	2-33460-2
----	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	LOOSE PIECE	33460

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
VOLTAGE RATING: NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.5mm² [13,100-20,800] CIR MILS SOLID OR STRANDED
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 3-24-93 TA BRINKMAN CHK 3-24-93 DA PATTERSON APPD 3-24-93 DE MILLER APPD 3-24-93 JL MECKLEY PRODUCT SPEC -
MATERIAL COPPER PER ASTM B-152 ANNEALED	
FINISH SEE TABLE	
QUANTITY	FINISH
50	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
----	UNPLATED
1000	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
1500	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
----	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
QUANTITY	FINISH
50	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
----	UNPLATED
1000	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
1500	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727
----	TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727

AMP AMP Incorporated Harrisburg, PA 17105-3608	
NAME TERMINAL, RING TONGUE, SOLISTRAND™	
SIZE C	CAGE CODE 00779
DRAWING NO C=33460	
SCALE 8:1	SHEET 1 OF 1