

# operating head 45 x 45 mm - black color - black handle - 2 - 0 - 1

KAC1H48

EAN Code: 3389110980523

#### Main

Range of product	Harmony Series K	
Product or component type	Cam switch operating head	
Component name	KAC	
Product compatibility	Front mounting bodies 12 and 20 A by Ø 22 mm hole	
Cam switch head type	With front plate 45 x 45 mm	
Type of operator	Black handle, length = 35 mm	
Rotary handle padlocking	Without	
Presentation of legend	With mat black legend, 2 - 0 - 1	
Switching angle	45 °	

## Complementary

Mechanical durability	1000000 cycles
CAD overall width	45 mm
CAD overall height	45 mm
CAD overall depth	77 mm
Length	35 mm
Net weight	0.012 kg
Compatibility code	KAC

### **Environment**

Protective treatment	TC	
Ambient air temperature for operation	-2555 °C	
Ambient air temperature for storage	-4070 °C	
Shock resistance	30 gn conforming to IEC 68-2-27	
Vibration resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)	
IP degree of protection	IP65 conforming to IEC 529	

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm

Package 1 Width	6.5 cm
Package 1 Length	8.0 cm
Package 1 Weight	58.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	16
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.134 kg

# **Logistical informations**

Country of origin CZ

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture		
Take-back	No	