

293577

Aluminium Handle, Ø31 mm,
1310 mm, Lime



Ergonomically designed with a comfortable grip and rounded top and hanger, this handle fits any Vikan product that requires a handle. Do not use with acid or chlorine.

Technical Data

Item Number	293577
Material	Anodised Aluminium Polypropylene
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	960 Pcs.
Quantity Per Layer (Pallet)	40 Pcs.
Box Length	1345 mm
Box Width	190 mm
Box Height	80 mm
Product Diameter	31 mm
Length/Depth	1310 mm
Width	31 mm
Height	31 mm
Gross Weight	0,52 kg
Net Weight	0,49 kg
Cubik metre	0,0013 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	8 pH
Recycling Symbol "7", Miscellaneous Plastics	No
GTIN-13 Number	5705022013704
GTIN-14 Number (Box quantity)	15705028013736
Commodity Code	76042910
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.