

Features

- Designed for fast, efficient flush cutting in metal.
- Featuring a 1.8mm tooth pitch, it delivers high-speed cutting performance ideal for pipes and profiles with wall thicknesses from 3mm to 8mm.
- Manufactured from tough M2 High Speed Steel, this blade is designed for cutting regular-strength steel and comes in a standard 225mm length, providing a cutting capacity of up to 175mm.

Reciprocating Saw Blade - Metal 225 x 19 x 0.9mm -Fast Cut

RS Stock No.: 0757827



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Reciprocating Saw Blade

0757827 Metal Reciprocating Saw Blade is designed for fast, efficient flush cutting in metal. Featuring a 1.8mm tooth pitch, it delivers high-speed cutting performance ideal for pipes and profiles with wall thicknesses from 3mm to 8mm. Manufactured from tough M2 High Speed Steel, this blade is designed for cutting regular-strength steel and comes in a standard 225mm length, providing a cutting capacity of up to 175mm.

- *Manufactured with D6A Shock-Resisting Tool Steel & M2 High Speed Steel*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Pipes, Profiles and Box Section*
- *Supplied in 5pc Packs*

General Specifications

Tooth Design	Side Set, Milled
Type	Reciprocating Saw Blade
Teeth Spacing	1.0mm
TPI	14
Thickness	0.9mm
Max Cut Depth	175mm
Cut Type	Fast Cutting
Blade Material	M2 High Speed Steel
Body Material	D6A Shock-Resisting Tool Steel
Fitting	S-Shank 1/2"
Length	225mm
Width	19mm

Stock No.	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	Precision Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757830	Fine Cutting	0.9mm	225mm	19mm

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	RS PRO	Reciprocating Saw Blade	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757830	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	225mm	19mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories