



Specification

Terminal Material	Tin Plated Copper Tube
Insulation Material	Polyamide
Max Temperature	105 °C
Max Voltage Max	600 V
Max Current	35 A
Wire Range	2 x 4 mm ²

Drawing



Ød1	3.7 mm
d2	8.8 mm
d3	4.9 mm
L1	23 mm
L2	12 mm
S1	0.20 mm
S2	0.45 mm

Art. Nr.
RND 465-01378